


119

Schlauchtülle konisch

Male hose adapter con.

	LW	R	H	L1	L2	
30402	6	R ¹ / ₈	88	19	31,5	12
30403	6	R ¹ / ₄	11	19	35	14
30404	7	R ¹ / ₈	8	19	31,5	12
30405	7	R ¹ / ₄	11	19	35	14
30406	8	R ¹ / ₈	8	19	31,5	12
30407	8	R ¹ / ₄	11	19	35	14
30408	9	R ¹ / ₈	8	19	31,5	12
30409	9	R ¹ / ₄	11	19	35	14
30410	9	R ³ / ₈	11,5	19	35,5	17
30411	9	R ¹ / ₂	14	19	38,5	22
30412	10	R ¹ / ₈	8	20	32,5	12
30413	10	R ¹ / ₄	11	20	36	14
30414	10	R ³ / ₈	11,5	20	36,5	17
30415	10	R ¹ / ₂	14	20	39,5	22
30416	12	R ¹ / ₄	11	20	36	14
30417	12	R ³ / ₈	11,5	20	36,5	17
30418	12	R ¹ / ₂	14	20	39,5	22
30419	14	R ³ / ₈	11,5	22	38,5	17
30420	16	R ³ / ₈	11,5	22	38,5	17
30421	14	R ¹ / ₂	14	22	41,5	22
30422	16	R ¹ / ₂	14	22	41,5	22
30426	17	R ¹ / ₂	14	24	43,5	22
30427	18	R ¹ / ₂	14	24	43,5	22