

Signal lamps with integrated filament lamp - 14 mm, round lens, 24 - 28 V, green lens
1.69.523.003/1502

Approvals

VDE VDE T85° (only version with neon lamp)

General information

 Form of lens round
 Colour of lens transparent green

Dimensions

 Dimensions of collar $\varnothing 18 \times 4$ mm
 Overall height 4 mm
 Mounting depth 31.5 mm
 Mounting hole 14 mm

Mechanical design

 Mounting pressing into hole
 Terminals quick connector 2.8 x 0.8 mm
 Lamp socket no
 Lamp filament lamp

Electrical characteristics

 Voltage limit max. 28 V
 Power limit max. 1.2 W

Other specifications

 Operating life 10,000 h
 Degree of protection from front side IP40
 Weight 5 g
 Approvals 1,5 mA (T °C) VDE, SEV, FEMKO, DEMKO

Panel cut-out


