

## Subminiatur - Glühlampen - Wire Terminal, T1¼

(4,1x11,5mm)

Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553...	Preis/St. in €
6V	40mA	0,24W	00900640	369006	1,00
12V	20mA	0,24W	00901520	368177	1,00
	30mA	0,36W	00901530	369020	0,90
	40mA	0,48W	00901540	369037	1,00
24V	35mA	0,84W	00902535	369082	1,00
	40mA	0,96W	00902540	369044	0,95
	50mA	1,2W	00902550	369051	0,90
28V	40mA	1,22W	00902840	369785	1,00



## Subminiatur - Glühlampen - Wire Terminal, T1½

(5,1x13,2mm)

Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553...	Preis/St. in €
6,3V	40mA	0,25W	00900740	369105	1,20
12V	40mA	0,48W	00901240	369112	1,00
	80mA	0,96W	00901280	369129	1,30
18V	40mA	0,72W	00901840	369143	1,20



## Subminiatur - Glühlampen - Wire Terminal, T1¾

(5,7x13,2mm)

Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553...	Preis/St. in €
6,3V	200mA	1,26W	00906320	369716	0,85
12V	40mA	0,48W	00901241	369723	0,85
14V	80mA	1,12W	00901481	369730	0,85
24V	40mA	0,96W	00902441	369747	0,90
	50mA	1,2W	00902451	369754	1,20
28V	40mA	1,12W	00902841	368368	0,85

