

Röhrenlampen

RL Sondergröße klar

Socket E14

(25 x 70 mm)

Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553....
220-260V		25W	00919416	242026
		40W	00919417	242002
235V	63mA	15W	00918216	242033
	106mA	25W	00918217	242019
	170mA	40W	00918218	242040



Röhrenlampen

RL

klar

Socket E14

(25 x 65 mm)

Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553....
130V	115mA	15W	00100701	242163
240V	63mA	15W	00100704	242170



Röhrenlampen

RL

Socket B22d

(22 x 50 mm)

Spannung	Ausführung	Leistung	Artikel-Nr.	EAN 4021553....
240V	klar	7,5W	00100825	243054
260V	klar	15W	00100826	243061



Nählicht-Röhrenlampen

stossfest

Socket E14

(22 x 57 mm)

Spannung	Ausführung	Leistung	Artikel-Nr.	EAN 4021553....
235V	i-matt	15W	00762215	292106
	i-matt	20W	00762220	292113

