



Sondertyp:

**T6,8K
(6,8 x 22 mm)**

auf Anfrage lieferbar !

Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553...
6V	20mA	0,12W	00540620	345000
	50mA	0,3W	00540650	345017
	80mA	0,48W	00540680	345024
	200mA	1,2W	00540618	345031
12V	20mA	0,24W	00541220	345048
	40mA	0,48W	00541240	345314
	50mA	0,54W	00541250	345055
	100mA	1,2W	00541210	345062
24V	20mA	0,5W	00542420	345079
	25mA	0,6W	00542425	345086
	40mA	1,0W	00542440	345093
	50mA	1,2W	00542450	345109
	80mA	2,0W	00542480	345116
28V	40mA	1,12W	00542840	345123
	45mA	1,26W	00542845	345130
	50mA	1,4W	00542850	345352
30V	20mA	0,6W	00543020	345284
	40mA	1,2W	00543040	345147
	50mA	1,5W	00543050	345154
	100mA	3,0W	00543010	345161
36V	20mA	0,72W	00543620	345178
	33mA	1,2W	00543633	345369
Grün	40mA	1,44W	00543640	345321
	40mA	1,44W	00543640-G	345376
	50mA	1,8W	00543650	345185
48V	20mA	1,0W	00544820	345192
	25mA	1,2W	00544825	345208
	40mA	1,4W	00544840	345215
	50mA	2,0W	00544850	345222
60V	20mA	1,2W	00546020	345239
	40mA	2,4W	00546040	345246
	60mA	3,6W	00546060	345338
70V	20mA	1,4W	00547020	345253
80V	20mA	1,6W	00548020	345345
Glimmlampe mit Widerstand				
230V			00542222	345260
Glimmlampe mit Widerstand grün				
230V			00542223	345277
Lampenzieher T2			01909005	

Abweichende Spannungen und Leistungen auf Anfrage lieferbar (VPE 100 Stück) !