



Sondertyp:

**T6,8K
(6,8 x 22 mm)**

auf Anfrage lieferbar !

| Spannung | Strom | Leistung | Artikel-Nr. | EAN 4021553... |
|---------------------------------------|-------|----------|-------------------|-------------------|
| 6V | 20mA | 0,12W | 00540620 | 345000 |
| | 50mA | 0,3W | 00540650 | 345017 |
| | 80mA | 0,48W | 00540680 | 345024 |
| | 200mA | 1,2W | 00540618 | 345031 |
| 12V | 20mA | 0,24W | 00541220 | 345048 |
| | 40mA | 0,48W | 00541240 | 345314 |
| | 50mA | 0,54W | 00541250 | 345055 |
| | 100mA | 1,2W | 00541210 | 345062 |
| 24V | 20mA | 0,5W | 00542420 | 345079 |
| | 25mA | 0,6W | 00542425 | 345086 |
| | 40mA | 1,0W | 00542440 | 345093 |
| | 50mA | 1,2W | 00542450 | 345109 |
| | 80mA | 2,0W | 00542480 | 345116 |
| 28V | 40mA | 1,12W | 00542840 | 345123 |
| | 45mA | 1,26W | 00542845 | 345130 |
| | 50mA | 1,4W | 00542850 | 345352 |
| 30V | 20mA | 0,6W | 00543020 | 345284 |
| | 40mA | 1,2W | 00543040 | 345147 |
| | 50mA | 1,5W | 00543050 | 345154 |
| | 100mA | 3,0W | 00543010 | 345161 |
| 36V | 20mA | 0,72W | 00543620 | 345178 |
| | 33mA | 1,2W | 00543633 | 345369 |
| Grün | 40mA | 1,44W | 00543640 | 345321 |
| | 40mA | 1,44W | 00543640-G | 345376 |
| | 50mA | 1,8W | 00543650 | 345185 |
| 48V | 20mA | 1,0W | 00544820 | 345192 |
| | 25mA | 1,2W | 00544825 | 345208 |
| | 40mA | 1,4W | 00544840 | 345215 |
| | 50mA | 2,0W | 00544850 | 345222 |
| 60V | 20mA | 1,2W | 00546020 | 345239 |
| | 40mA | 2,4W | 00546040 | 345246 |
| | 60mA | 3,6W | 00546060 | 345338 |
| 70V | 20mA | 1,4W | 00547020 | 345253 |
| 80V | 20mA | 1,6W | 00548020 | 345345 |
| Glimmlampe mit Widerstand | | | | |
| 230V | | | 00542222 | 345260 |
| Glimmlampe mit Widerstand grün | | | | |
| 230V | | | 00542223 | 345277 |
| Lampenzieher T2 | | | 01909005 | |

Abweichende Spannungen und Leistungen auf Anfrage lieferbar (VPE 100 Stück) !