

X-COM®**S**-SYSTEM

Vorkonfektionierte Federleisten

0,25 – 2,5 (4) mm² | AWG 22 – 12
 690 V/6 kV/3 ①
 I_N 24 (32) A *
 Modulbreite 5,2 mm / 0.205 in
 10 – 12 mm / 0.43 in

0,25 – 2,5 (4) mm² | AWG 22 – 12
 690 V/6 kV/3 ①
 I_N 24 (32) A *
 Modulbreite 5,2 mm / 0.205 in
 10 – 12 mm / 0.43 in

0,25 – 2,5 (4) mm² | AWG 22 – 12
 690 V/6 kV/3 ①
 I_N 24 (32) A *
 Modulbreite 5,2 mm / 0.205 in
 10 – 12 mm / 0.43 in



Polzahl	Bestell-Nr.	VPE	Polzahl	Bestell-Nr.	VPE	Polzahl	Bestell-Nr.	VPE
1-Leiter-Federleisten, kodierbar, grün-gelb, grau,			1-Leiter-Federleiste, kodierbar, grün-gelb, blau, grau,			1-Leiter-Federleiste, kodierbar, grün-gelb, blau, grau,		
3-polig	2022-103/000-036	50	3-polig	2022-103/000-038	50	5-polig	2022-105/000-038	50
1-Leiter-Federleisten, kodierbar, grau, grün-gelb			1-Leiter-Federleiste, kodierbar, grau, blau, grün-gelb,			1-Leiter-Federleiste, kodierbar, grau, blau, grün-gelb,		
3-polig	2022-103/000-037	50	3-polig	2022-103/000-039	50	5-polig	2022-105/000-039	50

* Strombelastbarkeitskurven auf Anfrage