

X-COM®**B**-SYSTEM-MINI

Federleisten zum Selbstkonfektionieren

Serie 2020

0,14 - 1 (1,5) mm² ① AWG 24 - 16
 500 V/6 kV/3 ②
 I_N 13,5 A ③
 Klemmenbreite 3,5 mm / 0.138 in
 9 - 11 mm / 0.39 in ④

0,14 - 1 (1,5) mm² ① AWG 24 - 16
 500 V/6 kV/3 ②
 I_N 13,5 A ③
 Klemmenbreite 3,5 mm / 0.138 in
 9 - 11 mm / 0.39 in ④



Bestellnr.	VPE	Bestellnr.	VPE
1-Leiter-Endmodul,		2-Leiter-Endmodul,	
kodierbar		kodierbar	
	2020-181 250		2020-281 250
	2020-184 250		2020-284 250
	2020-187 250		2020-287 250
1-Leiter-Anfangsmodul mit Abschlussplatte,		2-Leiter-Anfangsmodul mit Abschlussplatte,	
kodierbar		kodierbar	
	2020-161 250		2020-261 250
	2020-164 250		2020-264 250
	2020-167 250		2020-267 250
Zubehör, Federleisten			
passendes Beschriftungssystem WMB/Beschriftungsstreifen (siehe Kapitel 13)			
Warnabdeckung,			
mit schwarzem Blitzpfeil, für 5 Klemmen			
	gelb 2000-115 100 (4x25)		
Verriegelungsklinke,			
9,6 mm breit			
	orange 2022-152 100 (4x25)		
	grau 2022-151 100 (4x25)		
Verriegelungsklinke,			
4,8 mm breit			
	orange 2022-142 100 (4x25)		
	grau 2022-141 100 (4x25)		
Zugentlastungsplatte, grau			
	35 mm breit 734-326 100 (4x25)		
	6 mm breit 734-327 100 (4x25)		
	12,5 mm breit 734-328 100 (4x25)		
	25 mm breit 734-329 100 (4x25)		
WMB-Multibeschriftungssystem,			
10 Streifen à 10 Schilder pro Karte, für Klemmenbreite 3,5 mm			
	unbedruckt 793-3501 5		
Beschriftungsstreifen, unbedruckt,			
11 mm breit, 50m-Rolle			
	weiß 2009-110 1		