

# Konfektionierte Leitungen 3 x 1,5 mm<sup>2</sup> / 3 x 1 mm<sup>2</sup>

	<p>PVC H05VV-F 3x1,5 I<sub>N</sub> 16 A H05VV-F 3G1,0 I<sub>N</sub> 10 A ④</p> <p>250 V/4 kV/3</p> <p>② Zulassungen</p>																								
<p><b>Anschlussleitung, Buchse - SCHUKO-Stecker, abgewinkelt</b></p>	<p>Länge Bestellnr. schwarz Bestellnr. weiß</p> <p>● ○ Kodierung A PVC</p> <table border="1"> <tr><td>1 m</td><td>771-9993/306-101</td><td>.../306-102</td></tr> <tr><td>2 m</td><td>771-9993/306-201</td><td>.../306-202</td></tr> <tr><td>3 m</td><td>771-9993/306-301</td><td>.../306-302</td></tr> <tr><td>4 m</td><td>771-9993/306-401</td><td>.../306-402</td></tr> <tr><td>5 m</td><td>771-9993/306-501</td><td>.../306-502</td></tr> <tr><td>6 m</td><td>771-9993/306-601</td><td>.../306-602</td></tr> <tr><td>7 m</td><td>771-9993/306-701</td><td>.../306-702</td></tr> <tr><td>8 m</td><td>771-9993/306-801</td><td>.../306-802</td></tr> </table>	1 m	771-9993/306-101	.../306-102	2 m	771-9993/306-201	.../306-202	3 m	771-9993/306-301	.../306-302	4 m	771-9993/306-401	.../306-402	5 m	771-9993/306-501	.../306-502	6 m	771-9993/306-601	.../306-602	7 m	771-9993/306-701	.../306-702	8 m	771-9993/306-801	.../306-802
1 m	771-9993/306-101	.../306-102																							
2 m	771-9993/306-201	.../306-202																							
3 m	771-9993/306-301	.../306-302																							
4 m	771-9993/306-401	.../306-402																							
5 m	771-9993/306-501	.../306-502																							
6 m	771-9993/306-601	.../306-602																							
7 m	771-9993/306-701	.../306-702																							
8 m	771-9993/306-801	.../306-802																							
<p><b>Anschlussleitung, Stecker - SCHUKO-Kupplung</b></p>	<p>Länge Bestellnr. schwarz Bestellnr. weiß</p> <p>● ○ Kodierung A PVC</p> <table border="1"> <tr><td>1 m</td><td>771-9993/406-101</td><td>.../406-102</td></tr> <tr><td>2 m</td><td>771-9993/406-201</td><td>.../406-202</td></tr> <tr><td>3 m</td><td>771-9993/406-301</td><td>.../406-302</td></tr> <tr><td>4 m</td><td>771-9993/406-401</td><td>.../406-402</td></tr> <tr><td>5 m</td><td>771-9993/406-501</td><td>.../406-502</td></tr> <tr><td>6 m</td><td>771-9993/406-601</td><td>.../406-602</td></tr> <tr><td>7 m</td><td>771-9993/406-701</td><td>.../406-702</td></tr> <tr><td>8 m</td><td>771-9993/406-801</td><td>.../406-802</td></tr> </table>	1 m	771-9993/406-101	.../406-102	2 m	771-9993/406-201	.../406-202	3 m	771-9993/406-301	.../406-302	4 m	771-9993/406-401	.../406-402	5 m	771-9993/406-501	.../406-502	6 m	771-9993/406-601	.../406-602	7 m	771-9993/406-701	.../406-702	8 m	771-9993/406-801	.../406-802
1 m	771-9993/406-101	.../406-102																							
2 m	771-9993/406-201	.../406-202																							
3 m	771-9993/406-301	.../406-302																							
4 m	771-9993/406-401	.../406-402																							
5 m	771-9993/406-501	.../406-502																							
6 m	771-9993/406-601	.../406-602																							
7 m	771-9993/406-701	.../406-702																							
8 m	771-9993/406-801	.../406-802																							
<p><b>Verbindungsleitung, Stecker - Kaltgerätekupplung, abgewinkelt ④</b></p>	<p>Länge Bestellnr. schwarz Bestellnr. weiß</p> <p>● ○ Kodierung A PVC</p> <table border="1"> <tr><td>1 m</td><td>771-9993/805-101</td><td>.../805-102</td></tr> <tr><td>2 m</td><td>771-9993/805-201</td><td>.../805-202</td></tr> <tr><td>3 m</td><td>771-9993/805-301</td><td>.../805-302</td></tr> <tr><td>4 m</td><td>771-9993/805-401</td><td>.../805-402</td></tr> <tr><td>5 m</td><td>771-9993/805-501</td><td>.../805-502</td></tr> <tr><td>6 m</td><td>771-9993/805-601</td><td>.../805-602</td></tr> <tr><td>7 m</td><td>771-9993/805-701</td><td>.../805-702</td></tr> <tr><td>8 m</td><td>771-9993/805-801</td><td>.../805-802</td></tr> </table>	1 m	771-9993/805-101	.../805-102	2 m	771-9993/805-201	.../805-202	3 m	771-9993/805-301	.../805-302	4 m	771-9993/805-401	.../805-402	5 m	771-9993/805-501	.../805-502	6 m	771-9993/805-601	.../805-602	7 m	771-9993/805-701	.../805-702	8 m	771-9993/805-801	.../805-802
1 m	771-9993/805-101	.../805-102																							
2 m	771-9993/805-201	.../805-202																							
3 m	771-9993/805-301	.../805-302																							
4 m	771-9993/805-401	.../805-402																							
5 m	771-9993/805-501	.../805-502																							
6 m	771-9993/805-601	.../805-602																							
7 m	771-9993/805-701	.../805-702																							
8 m	771-9993/805-801	.../805-802																							
	<p><b>Zubehör</b></p> <p><b>Verriegelungsklinke, für „Fliegende Verbindungen“, mit Handbetätigung</b></p> <table border="1"> <tr><td>schwarz</td><td>770-101</td><td>100 (4 x 25)</td></tr> <tr><td>weiß</td><td>770-121</td><td>100 (4 x 25)</td></tr> </table> <p><b>Verriegelungsklinke, für „Fliegende Verbindungen“, mit Werkzeugbetätigung</b></p> <table border="1"> <tr><td>schwarz</td><td>770-111</td><td>100 (4 x 25)</td></tr> <tr><td>weiß</td><td>770-131</td><td>100 (4 x 25)</td></tr> </table> <p><b>Verschlussstück, für Stecker, teilbar, 5-polig</b></p> <table border="1"> <tr><td>gelb</td><td>770-360</td><td>100</td></tr> </table> <p><b>Kodierstift, für Stecker</b></p> <table border="1"> <tr><td>grau</td><td>770-401</td><td>100</td></tr> </table>	schwarz	770-101	100 (4 x 25)	weiß	770-121	100 (4 x 25)	schwarz	770-111	100 (4 x 25)	weiß	770-131	100 (4 x 25)	gelb	770-360	100	grau	770-401	100						
schwarz	770-101	100 (4 x 25)																							
weiß	770-121	100 (4 x 25)																							
schwarz	770-111	100 (4 x 25)																							
weiß	770-131	100 (4 x 25)																							
gelb	770-360	100																							
grau	770-401	100																							