




The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.



55183X (2:1)



55184X (1:1)



Veredelung:  
 5518XT - Cu2/Sn5  
 5518XN - Cu2,5/Ni2,5 Sulfamat  
 Beschichtungen konform zu ROHS-Richtlinie  
 und zum Elektroggesetz



55183X	M3 6h
55184X	4-40 UNC 3A
Artikel-Nr.	d

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksmusterertragung vorbehalten.

Toleranzen / tolerances: DIN ISO 2768 m				Projektion / projection: 		Maßstab / scale: 4:1		Werkstoff / material: 11SMnPb30			
								Oberfläche cm² / surface cm²: 2,4			
								Veredelung / refinement: siehe Text			
								Gewicht / weight: 1,2 g			
				Maßangaben in: dimension units mm		Artikel / article: <b>Verriegelungsschraube für 17-Kunststoffhauben</b>					
				Datum / date						Name / name	
				Bearb / drawn						Schulz	
				Gepr / checked		Strauch					
08	alt Cu2/Ni5	21.03.13	Ast	<b>PROVERTHA</b> CONNECTORS, CABLES & SOLUTIONS		Zeichnungs-Nr. / drawing no: 5518XX-Z			Blatt / sheet: 1/1		
07	alt 5518M25X	26.04.12	Ast			Ersatz für / substitute to: 5518XX			DIN A4		
06	neu gezeichnet	09.11.11	Ast								
Index	Änderung / modification		Datum	Name	Kd.-Zg.						