



5

4

3

2

1



Bestell-Nummer / Part No.		D	Leiterquerschnitt wire gauge		Abisolierlänge der Litze stripping length
versilbert silver plated	vergoldet gold plated		mm ²	AWG	
09 15 000 6204	09 15 000 6224	0,90	0,14-0,37	26-22	8
09 15 000 6203	09 15 000 6223	1,10	0,5	20	
09 15 000 6205	09 15 000 6225	1,30	0,75	18	
09 15 000 6202	09 15 000 6222	1,45	1	18	
09 15 000 6201	09 15 000 6221	1,75	1,5	16	
09 15 000 6206	09 15 000 6226	2,25	2,5	14	6
09 15 000 6207		0,90	0,14-0,37	26-22	8

1) Nur für Buchanan Crimpwerkzeug Einstellø 1,0/
only for Buchanan crimping tool adjusting ø0,1



All Dimensions in mm
Original Size DIN A 4

Techn. Character.

Nicht tolerierte Masse / Free size tolerances

	Dat.	Name	Masstab / Scale
Detail.	22.03.99	Kö	2:1
Insp.		SDT	
Stand.			

Han D / R15 Buchsenkontakt
Crimpkontakt gedreht 10A
crimpcontact twisted 10A

410609	15.07.03	DY
25592		
Mod.	Dat.	Name

HARTING Electric GmbH & Co. KG
D-32339 Espelkamp



TB 09 15 000 62..

Blatt / page

Sub.