



Anwendungshinweis

V 2499

# Hebelcrimpzangen-Satz

Operation Instructions

## Quick Change Ratchet Crimper Kit













V 2499 AH

**ViGOR GmbH** • ☒ 10 04 61 • D-42804 Remscheid • Germany

☎ +49 (0) 21 91 / 97 95 • ☎ +49 (0) 21 91 / 97 96 00 • ✉ info@vigor-equipment.com • 🌐 www.vigor-equipment.com

# 1. BESCHREIBUNG DESCRIPTION

<b>A</b>		<b>Wechselkopf Changeable Head A:</b> <ul style="list-style-type: none"><li>• Für isolierte Kabelschuhe</li><li>• <i>Insulated terminal</i></li></ul>
<b>B</b>		<b>Wechselkopf Changeable Head B:</b> <ul style="list-style-type: none"><li>• Für nicht isolierte Kabelschuhe</li><li>• <i>Non-Insulated Terminal</i></li></ul>
<b>C</b>		<b>Wechselkopf Changeable Head C:</b> <ul style="list-style-type: none"><li>• Für nicht isolierte Flachsteckerhülsen</li><li>• <i>Open Barrel Terminal</i></li></ul>
<b>D</b>		<b>Wechselkopf Changeable Head D:</b> <ul style="list-style-type: none"><li>• Für Aderendhülsen mit Kunststoffkragen</li><li>• <i>Cord End terminal</i></li></ul>
<b>F</b>		<b>Wechselkopf Changeable Head F:</b> <ul style="list-style-type: none"><li>• Für Aderendhülsen mit Kunststoffkragen</li><li>• <i>Cord End terminal</i></li></ul>

ANWENDUNG	APPLICATION	ABMESSUNG	WAIST
A		A	AWG 22-18/16-14/12-10 0.5-1.0/1.5-2.5/4.0-6.0 mm <sup>2</sup>
B		B	AWG 20-18/16-14/12-10/8.0 1.5/2.5/6.0/10 mm <sup>2</sup>
C		C	AWG 20-18/16-14/12-10 0.5-1.0/1.5-2.5/4.0-6.0 mm <sup>2</sup>
D		D	AWG 22/20/18/16/14/12 0.5/0.75/1.0/1.5/2.5/4.0 mm <sup>2</sup>
F		F	AWG 10/8.0/6.0 6.0/10/16 mm



## BESCHREIBUNG

- **Anwendungsbereich:**  
DIN-Kabelschuhe, Flachstecker, Flachsteckerhülsen und Aderendhülsen.
- Verarbeitung von Leiter- und Isolationscrimp in einem Arbeitsgang
- Intensiver Isolationscrimp mit spezieller Profilgeometrie
- Integrierte Zwangssperre, sichert das vollständige Crimpen
- Ergonomische Hand-Softgriffe
- Leichte Handhabung
- Einfacher Profiltausch, vielseitig einsetzbar
- Aus hochfesten Spezial Stahl
- Länge: 220 mm; Breite: 70 mm
- Gewicht: 510 g

## DESCRIPTION

- **Application fields:**  
DIN cable lugs, flat pin terminals, flat pin bushings and cable end sleeves.
- Crimping of conductor crimp and insulation crimp in one working step
- Intensive insulation crimp with special profile geometry
- Integrated lock mechanism provides complete crimp
- Ergonomic soft grip handles
- Easy handling
- Easy changeable heads, multifunctional
- Made of high-strength special steel
- Length: 220mm, width: 70mm
- Weight: 510g.