

Vierkantmuttern

DIN 562

Niedrige Vierkantmuttern



Maße	M 2	M 2,5	M 3	M 4	M 5	M 6	M 8	M 10
m	1,2	1,6	1,8	2,2	2,7	3,2	4	5
s	4	5	5,5	7	8	10	13	16/17*