



















Waterfall *Set 30/Set 60 Solo/Waterfall 30/60/90*

- DK Brugsanvisning
- NO Bruksanvisning
- SE Bruksanvisning
- FI Käyttöohje
- HU Használati útmutató
- PL Instrukcja użytkowania
- CZ Návod k použití









Waterfall 30 Set














15737






Waterfall Set 60 Solo



kg 15.00 kg












15737

Waterfall 30 | Waterfall 60 | Waterfall 90







Waterfall 30
















Waterfall 60




Waterfall 90



	Waterfall 30		Waterfall 60		Waterfall 90	
	 Classic	 Premium	 Classic	 Premium	 Classic	 Premium
	 $l \leq 3 \text{ m}$ $\varnothing 1 \text{ in}$		 $l \leq 3 \text{ m}$ $\varnothing 1 \text{ in}$		 $l \leq 3 \text{ m}$ $\varnothing 1\frac{1}{4} \text{ in}$	
1.00 m	3500	4000	5500	4000 6000	8500	6000 8000
0.80 m	3500	4000	5500	4000 6000	5500 8500	4000 6000 8000
0.60 m	2500	—	3500	4000	5500 8500	4000 6000
0.40 m	2500	—	3500	4000	5500	4000 6000
0.20 m	2500	—	3500	—	5500	4000 6000



Pos.	Waterfall		
	30	60	90
1	15737	15737	16757



1



OASE GmbH · www.oase-livingwater.com

Tecklenburger Straße 161 · 48477 Hörstel · Postfach 20 69 · 48469 Hörstel · Germany