



Montagewinkel Metall, inklusive M20 Kabelverschraubung

Typ SL7/4-FW-T
Katalog Nr. 171455
Alternate Catalog No. SL7/4-FW-T

Lieferprogramm

Sortiment			Zusatzrüstung
Grundfunktion Zubehör			Montagewinkel inklusive M20 Kabelverschraubung
Material			Edelstahl (Winkel) Aluminium (Gewindeadapter)
Montageart			für vertikale Montage
			Dichtung im Lieferumfang
verwendbar für			SL4-PIB-T... SL7-CB-T...
Anbindung an SmartWire-DT			nein

Daten für Bauartnachweis nach IEC/EN 61439

Technische Daten für Bauartnachweis			
Min. Betriebsumgebungstemperatur		°C	-30
Max. Betriebsumgebungstemperatur		°C	60

Technische Daten nach ETIM 7.0

Niederspannungsschaltgeräte (EG000017) / Signalsäulenelement, Befestigungswinkel (EC001153)			
Elektro-, Automatisierungs- und Prozessleittechnik / Niederspannungs-Schalttechnik / Befehls- und Meldegerät / Signalsäulenelement, Befestigungswinkel (ecl@ss10.0.1-27-37-12-33 [AKF051014])			
Montageart			Wandmontage
Farbe			sonstige

Approbationen

Product Standards			IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
UL File No.			E29184
UL Category Control No.			NKCR
CSA File No.			UL report applies to both US and Canada
CSA Class No.			NKCR7
North America Certification			UL listed, certified by UL for use in Canada
Degree of Protection			UL Type 4, 4X, 13

Abmessungen

