



The innovative Sliding full-motion mount places 37"-70" TVs just 45 mm from the wall, yet still allows full-motion capabilities. Support up to 40kgs/88lbs, it also passes a four times weight test. This mount slides to extend out up to 680mm from wall and allows large TV to swivel left and right up to 90 degree. Post-installation level adjustment allows the TV to "roll" up to 30 clockwise and counterclockwise to ensure it is perfectly level. The LPA35-462 always has a finished appearance with a decorative cover that conceals assembly and mounting hardware.

NO locked function!

Product Feature

- No Tool Assembly allows assembling in minutes with no tools required
- Sliding long arm offers maximum viewing flexibility
- Built-in level adjustment ensures perfect positioning
- Decorative cover conceals assembly and mounting hardware for a finished appearance

Technical data

Specification: full motion

By Grade: Premium Series

By Function: Full Motion

By Mounting Pattern: Universal

Material: Aluminum, Steel

Available Color: Black

Product Size: 824X430X56mm

Recommended Screen Size: 37"-70"

Installation: Solid wall, Single Stud

Rated Weight Capacity: 40kgs/88lbs

Strength tested: 4 times approved

Max.Hole Pattern: 648x400mm

VESA Standard: 200x200, 300x200, 300x300, 400x300, 400x200,
400x400

Max.VESA: 600x400

Tilt: -12°~+8°

Swivel: -90°~+90°

Level Adjustment: -3°~+3°

Profile: 45-680mm

Bubble Level: No

Anti-theft: No

Cable Management: No

Wall separated: No

Panel separated: No

AV Component Mount: No

Freely Positioned: Yes

Standard data

- weight of unit : 5.14kg
- A (unit) x 1
- B (fixed arm) x 2
- C (clip) x 2
- D (Alley key) x 1
- E (wrench) x 1
- M5x14 x4
- M6x14 x4
- M8x20 x 4
- M6x30 x 4
- M8x30 x 4
- M-F (connecting part) x 4
- M-G (spacer) x 8
- M-H (spacer) X 4
- ST6.3X60 (W-A) x 3
- W-B (concrete anchor) x 3
- W-C (washer) x 1
- manual

