



Artikelnummer	Artikelbezeichnung	Spannung	Nennleistung	Lebensdauer	Sockel	Farbtemperatur	Design
# 89503995	OMNILUX UV	240 V	11 W	5000h	E-14	6000 K	CFL ES
# 89504005	OMNILUX UV	240 V	15 W	5000h	E-27	6000 K	CFL ES
# 89506005	OMNILUX UV	240 V	20 W	5000h	E-27	6000 K	CFL ES
# 89507005	OMNILUX UV	240 V	25 W	8000h	E-27	6000 K	CFL ES
# 89507705	OMNILUX UV	240 V	85 W	8000h	E-27	6000 K	CFL ES
# 89507706	OMNILUX UV	240 V	85 W	8000h	E-27	6000 K	CFL ES
# 89507805	OMNILUX UV	240 V	105 W	8000h	E-27	6000 K	CFL ES
# 89507806	OMNILUX UV	240 V	105 W	8000h	E-27	6000 K	CFL ES
# 89510005	OMNILUX UV	240 V	75 W	1000h	E-27	6000 K	R-80
# 89510105	OMNILUX UV	240 V	75 W	1000h	E-27	6000 K	Skull 8cm
# 89511005	OMNILUX UV	240 V	75 W	1000h	E-27	6000 K	A 19 Bulb
# 89511015	OMNILUX UV	240 V	25 W	1000h	E-14	6000 K	R-50
# 89511025	OMNILUX UV	240 V	40 W	1000h	E-14	6000 K	C-35
# 89511035	OMNILUX UV	240 V	40 W	1000h	E-14	6000 K	G-45
# 89512005	OMNILUX UV	240 V	125 W	2500h	E-27	6000 K	ED17
# 89512020	SYLVANIA UV	240 V	125 W	2500h	E-27	6000 K	ED17
# 89513005	OMNILUX UV	240 V	160 W	1500h	E-27	6000 K	ED17
# 89513020	SYLVANIA UV	240 V	160 W	1500h	E-27	6000 K	ED17
# 89513505	OMNILUX UV	240 V	250 W	2500h	E-40	6000 K	ED37
# 89513515	SYLVANIA UV	240 V	250 W	2500h	E-40	6000 K	ED37
# 89514005	OMNILUX UV	240 V	400 W	2500h	E-40	6000 K	BT56
# 89514010	SYLVANIA UV	240 V	400 W	2500h	E-40	6000 K	BT56
# 89530005	OMNILUX R7S	240V	250 W	500h	R7-s	5500 K	Burner
# 88540464	OMNILUX LED 18	230 V	5 W	20000h	GU-10		Reflektor
# 88540579	OMNILUX LED 48	230 V	8 W	20000h	GU-10		Reflektor
# 88540599	OMNILUX LED 60	230 V	9 W	20000h	GU-10		Reflektor
# 88555516	OMNILUX JDR LED 18	230 V	1 W	20000h	E-27		Reflektor
# 91203464	OMNILUX LED 18	12 V	1,5 W	20000h	GX-5,3		Reflektor