





Frontseitig aufschraubbare Überspannungsbegrenzer Kompaktschütze CWC07-CWC025

Bild	verwendbar für	Schaltbild	Spannung	Typ	Gewicht
	CWC07-025 + CWCA0 CWC07-016 + CWCA0		12-24 V 50/60Hz 24-48 V 50/60Hz 50-127 V 50/60Hz 130-250 V 50/60Hz 275-380 V 50/60Hz 400-510 V 50/60Hz 180-230V 50/60Hz (empfohlen in Stromkreisen mit Restströmen > 1,4 mA)	RCC0-1 D49 RCC0-2 D53 RCC0-3 D55 RCC0-4 D63 RCC0-5 D84 RCC0-6 D73 RCAC0 D87	9 8
	CWC07-025 + CWCA0		12-48V 50/60Hz/12-60VDC 50-127 V 50/60Hz/60-180VDC 130-275 V 50/60Hz/180-300VDC 277-380 V 50/60Hz/300-510VDC 400-510 V 50/60Hz	VRC0-1 E01 VRC0-2 E34 VRC0-3 E38 VRC0-4 E41 VRC0-4 D73	8
	CWC07-016 + CWCA0		12-600VDC Zenerdiode 12-250VDC	DIC0-1 C33 DIZC0 C26	8