

LANYARD⁺

🔌 Reference: LANY-PLUS

🔌 Applications:

- With the same dimensions as the Basic, it provides twice the power.
- Quickly charges phones, smartphones, tablets, cameras and rechargeable batteries.
- Powers up to 20 LED bulbs.
- Allows recharging and illumination simultaneously.
- Powers USB devices and low-power devices at 12V.



🔌 Technical specifications:

Weight:	562gr
Dimensions:	Height: 65mm, ø: 100mm.
Maximum power:	20 W
Maximum voltage:	15 V
Power delivery at standard operating range:	10 W
Autonomy:	50.000 h. of continuous use
Operation temperature:	150 °C - 400 °C
Average consumption:	50gr. of gas or kerosene/h

🔌 Kit contents:

- Lanyard +
- 12V / USB Converter.
- Neoprene rubber bag.
- Operating instructions.

🔌 Available colours: ●

