



DMX-510USB

Order No.: 38.2440

RRP *

PRODUCTINFOS

DMX controller,

consisting of DMX controller software and USB DMX converter box.
With galvanic isolation between USB input and DMX output.

Features of controller software:

- Easy-to-use graphical user interface
- 510 DMX control channels
- 42 operating levels with 12 channel faders each + 1 level with 6 channel faders for adjusting the DMX parameters, 1 flash button for each channel fader
- 1 master fader, can be assigned to each channel as desired
- 500 programmable scenes can be stored per block
- Different scene blocks can be combined
- Stored scenes can also be activated via keyboard
- Music-controlled via sound card

- Function keys can be occupied with scenes and sequences (10 levels x 12)
- Automatic run of 4 parallel sequences with up to 500 scenes each
- Any number of groups can be stored with up to 60 channels each
- Synchronous groups can be created
- LED PAR colour control
- Individual stage background can be created with unit icons
- Blackout function
- Channel inversion
- Macro function for automatically generating figures (circle, eight, spiral lines, etc.) with the facility of 8 parallel macro runs
- Libraries can be created for DMX devices, a library is available containing every DMX device from IMG STAGELINE
- German, English, French and Spanish version

Specifications controller box:

- 510 DMX channels
- Connections: 1 x USB type B, 1 x 3-pole XLR, 1 x 5-pole XLR, 1 x low-voltage jack
- Dimensions: 115 x 103 x 40 mm, weight: 250 g
- Power is provided via enclosed power supply

Scope of delivery:

- DMX converter box
- Program CD with controller software and USB installation routine (with instructions on the CD)
- Plug-in power supply
- USB cable

System requirements:

IBM-compatible PC (Pentium 1 GHz or higher), 512 MB RAM, 20 MB free hard disk space, CD-ROM, USB port (USB 1.1 or higher), Windows® 2000/XP/Vista/7/8/10

When using no-name DMX products, it is recommended to use DMX-510USB with galvanic isolation of the input and output in order to prevent damage to the computer in case a fault occurs.

TECHNICAL SPECIFICATIONS

DMX-510USB

Type	DMX controller
DMX interface	DMX512
No. of DMX channels	510
No. of DMX outputs	1
No. of channel faders	510
Master fader	1
No. of scenes	500
Galvanic isolation	yes
Blackout function	yes
Music-controlled	via sound card
Special features	control via software
USB	yes
Power supply	encl. plug-in power supply
Dimensions	115 x 40 x 103 mm
Width	115 mm
Height	40 mm
Depth	103 mm
Admiss. ambient temp.	0-40 °C
Weight	250 g
Connections	1 x 3-pole XLR, 1 x 5-pole XLR (DMX out), 1 x USB Type-B

* **Important Notice:** The retail prices shown here are non-binding recommendations that retailers can charge their customers. They are not part of any specific offer or advertisement. These prices include all charges as well as VAT, but do not cover any additional delivery and shipping costs. Our latest price lists for the retail market include all applicable delivery and payment terms for retailers.