

Technical data

LNT1200

MAX:57.5MM

A:155MM

B:204MM(A+49MM bracket)

C:230MM(A+49MM+26MM 2 piece bracket)

D:121MM

E:55MM

LNT1100

MAX:57.5MM

A:155MM

Without size of B as this size only have 1pcs 30mm bracket

C:185MM(A+30MM bracket)

