



**Designation:** 18703 101 421

**Battery Requirement:** 4x AA

**Bulb required:** 1pcs XPG2 R4 cool white LED

**Luminous intensity:** High: 215 lumens or 5756 cd  
Low: 45 lumens or 3600 cd

**Range:** 151m High / 120m Low  
(calculated distance at maximum luminous intensity with an illuminance of 0.25 lux)

**Weight:** 238g (without batteries)

**Material:** Aluminum  
PC (Polycarbonate)  
TPE (Thermoplastic Rubber)  
All contact parts made of aluminium, bronze or nickel plated steel

<b>Dimensions (mm):</b>	<b>A</b>	<b>38.5</b>
	<b>B</b>	<b>50.5</b>
	<b>C</b>	<b>50.8</b>
	<b>D</b>	<b>42.5</b>
	<b>E</b>	<b>192</b>

**Run Time:** High: 8 hours (with VARTA HE)  
Low: 72 hours (with VARTA HE)

**Features:**

- Super bright CREE cool white LED
- Push switch(High/Low/Off)
- High impact rubber(TPE) head & tail cap for maximum durability
- Type II anodized
- Comfortable handle with ergonomic design with thumb rest area built in
- 180° swivel head to aim beam where needed.
- Hanging ring on endcap & Magnetic clip design for convenient hang-up storage.
- Battery low power indicator to remind users to replace battery timely (Red LED light on when 10% battery is left)
- IPX4 water resistant
- 4 meters drop test(with magnetic holder)
- 10,000 Switch cycle life

**No publication or circulation of data to third parties without consent of VARTA Consumer Batteries**