

Stirnräder aus Polyacetal (POM)

Modul 0,5

Ausführung: geradverzahnt, gespritzt, Eingriffswinkel 20°, Bohrung spanabhebend bearbeitet.
Maßänderung vorbehalten.

Anzahl Zähne	b [mm]	Ød [mm]	ØTK [mm]	Ødk [mm]	ØD [mm]	L [mm]	ØFM [mm]	c [mm]	G [g]	DM** [Ncm]	Art.-Nr.
12	3	2	6	7	4	7	-	3	0,14	1,41	SH0512HF
13	3	2	6,5	7,5	4	7	-	3	0,16	1,53	SH0513HF
14	3	2	7	8	5	7	-	3	0,22	1,65	SH0514HF
15	3	3	7,5	8,5	6	10	-	3	0,34	1,77	SH0515HF
16	3	3	8	9	6	10	-	3	0,35	1,88	SH0516HF
17	3	3	8,5	9,5	6	10	-	3	0,39	2	SH0517HF
18	3	4	9	10	7,8	10	-	3	0,53	2,12	SH0518HF
19	3	4	9,5	10,5	7,8	10	-	3	0,57	2,24	SH0519HF
20	3	4	10	11	7,9	10	-	3	0,6	2,36	SH0520HF
21	3	4	10,5	11,5	8	10	-	3	0,63	2,47	SH0521HF
22	3	4	11	12	10	10	-	3	0,92	2,59	SH0522HF
23	3	4	11,5	12,5	9,9	10	-	3	0,95	2,71	SH0523HF
24	3	4	12	13	9,9	10	-	3	0,99	2,83	SH0524HF
25	3	4	12,5	13,5	9,9	10	-	3	1,03	2,95	SH0525HF
26	3	4	13	14	9,9	10	-	3	1,08	3,06	SH0526HF
27	3	4	13,5	14,5	9,9	10	-	3	1,12	3,18	SH0527HF
28	3	4	14	15	10	10	-	3	1,2	3,3	SH0528HF
30	3	4	15	16	11,9	10	-	3	1,55	3,53	SH0530HF
32	3	4	16	17	12	10	-	3	1,68	3,77	SH0532HF
35	3	4	17,5	18,5	12	10	-	3	1,86	4,12	SH0535HF
36	3	4	18	19	11,9	10	-	3	1,9	4,24	SH0536HF
38	3	4	19	20	12	10	-	3	2,01	4,48	SH0538HF
40	3	4	20	21	12	10	14,8	2	2,01	4,71	SH0540HF
42	3	4	21	22	12,15	10	17	2	2,14	4,95	SH0542HF
45	3	4	22,5	23,5	12,15	10	18	2	2,33	5,3	SH0545HF
48	3	6	24	25	15	10	19	2	3,03	5,65	SH0548HF
50	3	6	25	26	15	10	20	2	3,11	5,89	SH0550HF
52	3	6	26	27	15	10	21	2	3,24	6,13	SH0552HF
54	3	6	27	28	15	10	21	2	3,43	6,36	SH0554HF
55	3	6	27,5	28,5	15	10	23	2	3,47	6,48	SH0555HF
56	3	6	28	29	15	10	23	2	3,61	6,6	SH0556HF
60	3	6	30	31	15	10	23	2	3,88	7,07	SH0560HF
64	3	6	32	33	15	10	23	2	4,33	7,54	SH0564HF
65	3	6	32,5	33,5	15	10	23	2	4,42	7,66	SH0565HF
70	3	6	35	36	15	10	29	2	4,62	8,25	SH0570HF
72	3	6	36	37	15	10	30	2	4,89	8,48	SH0572HF
75	3	6	37,5	38,5	15	10	33	2	4,86	8,84	SH0575HF
80	3	6	40	41	15	10	33	2	5,68	9,42	SH0580HF
90	3	6	45	46	15	10	39	2	6,55	10,6	SH0590HF
96	3	6	48	49	15	10	42	2	6,9	11,31	SH0596HF
100	3	6	50	51	15	10	44	2	7,51	11,78	SH05100HF
120	3	6	60	61	15	10	54	2	10,29	14,14	SH05120HF



Abbildung beispielhaft

