

Stirnräder aus Polyacetal (POM)

Modul 1,0

Ausführung: geradverzahnt, gespritzt, Eingriffswinkel 20°, Bohrung spanabhebend bearbeitet.
Maßänderung vorbehalten.



Abbildung beispielhaft

Anzahl Zähne	b [mm]	Ød [mm]	ØTK [mm]	Ødk [mm]	ØD [mm]	L [mm]	ØFM [mm]	c [mm]	G [g]	DM** [Ncm]	Art.-Nr.
12	9	4	12	14	9	17	-	9	1,68	16,96	SH1012HF
13	9	4	13	15	9	17	-	9	2,04	18,38	SH1013HF
14	9	4	14	16	9	17	-	9	2,16	19,79	SH1014HF
15	9	4	15	17	9	17	-	9	2,5	21,21	SH1015HF
16	9	4	16	18	9	17	-	9	2,74	22,62	SH1016HF
17	9	4	17	19	9	17	12	6	2,8	24,03	SH1017HF
18	9	4	18	20	9	17	13	6	3,26	25,45	SH1018HF
19	9	4	19	21	9	17	13	6	3,56	26,86	SH1019HF
20	9	4	20	22	9	17	13	6	4	28,27	SH1020HF
21	9	5	21	23	12	17	16	6	4,84	29,69	SH1021HF
22	9	5	22	24	12	17	16	6	5,2	31,1	SH1022HF
23	9	5	23	25	12	17	16	6	5,67	32,52	SH1023HF
24	9	6	24	26	15	18	18,5	6	6,59	33,93	SH1024HF
25	9	6	25	27	15	18	18,5	6	7,25	35,34	SH1025HF
26	9	6	26	28	15	18	18,5	6	7,49	36,76	SH1026HF
27	9	6	27	29	15	18	18,5	6	8,17	38,17	SH1027HF
28	9	6	28	30	15	18	21	6	8,3	39,58	SH1028HF
30	9	6	30	32	15	18	21	6	9,49	42,41	SH1030HF
32	9	6	32	34	18	18	23,5	4,6	11,26	45,24	SH1032HF
35	9	8	35	37	18	18	23,5	4,6	12,71	49,48	SH1035HF
36	9	8	36	38	18	18	27	4,6	12,44	50,89	SH1036HF
38	9	8	38	40	18	18	27	4,6	14,14	53,72	SH1038HF
40	9	8	40	42	18	18	27	4,6	15,37	56,55	SH1040HF
42	9	8	42	44	18	18	27	4,6	16,79	59,38	SH1042HF
45	9	8	45	47	18	18	36,5	4,6	16,15	63,62	SH1045HF
48	9	8	48	50	18	18	36,5	4,6	19	67,86	SH1048HF
50	9	8	50	52	18	18	36,5	4,6	20,56	70,69	SH1050HF
52	9	8	52	54	21	18	46	4,6	20,62	73,51	SH1052HF
54	9	8	54	56	21	18	46	4,6	22,28	76,34	SH1054HF
55	9	8	55	57	21	18	46	4,6	23,58	77,75	SH1055HF
56	9	8	56	58	21	18	46	4,6	25,14	79,17	SH1056HF
58	9	8	58	60	21	18	46	4,6	26,43	82	SH1058HF
60	9	8	60	62	21	18	46	4,6	28,98	84,82	SH1060HF
64	9	10	64	66	21	18	56,5	4,6	33,91	90,48	SH1064HF
65	9	10	65	67	21	18	56,5	4,6	36,06	91,89	SH1065HF
70	9	10	70	72	21	18	56,5	4,6	41,71	98,96	SH1070HF
72	9	10	72	74	21	18	66	4,6	39,31	101,79	SH1072HF
75	9	10	75	77	21	18	66	4,6	44,43	106,03	SH1075HF
80	9	10	80	82	21	18	66	4,6	52,62	113,1	SH1080HF
85	9	10	85	87	21	18	66	4,6	59,54	120,17	SH1085HF
90	9	10	90	92	21	18	76	4,6	66,32	127,23	SH1090HF
100	9	12	100	102	24	18	86	4,6	68,64	141,37	SH10100HF
110	9	12	110	112	24	18	96	4,6	83	155,51	SH10110HF
120	9	12	120	122	24	18	105,5	4,6	95,59	169,65	SH10120HF
130	9	12	130	132	24	18	115	4,6	109,7	183,78	SH10130HF
140	9	12	140	142	24	18	125	4,6	124,21	197,92	SH10140HF

