

F-Stecker

F-Stecker (Connector)

EMK 01	273167
EMK 02	21210014
EMK 11	273263
EMK 12	21210018
EMK 15	273276
EMK 17	273291
EMK 18	21210013
EMK 19	21210019



Typ Bestell-Nr.	Bezeichnung	Schirmungsmaß		Passend für Kabel	Verpackungs-Einheit/ Gewicht (St./kg)
EMK 01 273167	Schraubstecker	> 90 dB		LCD 90, 95, 99, 111	10 (100, 2000)/ 0,01
EMK 02 21210014	Schraubstecker	> 90 dB		LCD 90, 95, 99, 111	10 (100, 2000)/ 0,05
EMK 11 273263	Crimp-Stecker	> 90 dB		LCD 90, 95, 99, 111	10 (100, 2000)/ 0,03
EMK 12 21210018	Kompressions- Stecker	> 120 dB (5-862 MHz) > 90 dB (862-2400 MHz)		LCD 90, 95, 99, 111	100 (2000)/ 0,92
EMK 15 273276	Schraubstecker	> 90 dB		LCD 89	10 (100)/ 0,08
EMK 17 273291	Schraubstecker	> 90 dB		LCM 14, 17	10 (100)/ 0,2
EMK 18 21210013	Crimp-Stecker	> 90 dB		LCM 14, 17	10 (100)/ 0,14
EMK 19 21210019	Kompressions- Stecker	> 120 dB (5-862 MHz) > 90 dB (862-2400 MHz)		LCM 14, 17	50 (1000)/ 2,5