


KERN EWJ 300-3

High-quality precision balance with automatic internal adjustment

KERN



Category

Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	EWJ

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	300 g
Automatic adjustment - Standard time interval	2 h
Readability [d]	0,001 g
Reproducibility	0,003 g
Linearity	± 0,005 g
Resolution	300.000

Adjustment options	Internal calibration (automatic)
Recommended adjusting weight	300 g (F1)
Possible calibration points	100 g; 200 g; 300 g
Stabilization time	2 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,004 g

USP Minimum weight of sample (k = 2, U = 0.1%)	6 g
Construction type of the scale	Single-range balance

Units	kg
	g
	t
	gn
	dwt
	tl (Tw)
	tl (HK)
	ozt
	tl (Singap, Malays)

ct
mo
lb
oz
ffa
m

Maximum creep (15 minutes)	10 mg
Maximum creep (30 minutes)	20 mg
Default unit	g
Loadcell type	aluminium IP65 silicone-coated

Display

Display type	LCD
Display backlight	✓
Display screen size	129×27
Display digit height	21 mm
Languages of the user interface	English Symbol language

Construction

Dimension housing (W×D×H)	220×340×90 mm
Dimensions completely mounted (W×D×H)	220×340×180 mm
Dimensions rectangular draught shield - inner (W×D×H)	134×128×80 mm
Dimensions rectangular draught shield - outer (W×D×H)	144×139×81 mm
Dimensions weighing surface (Ø)	80 mm
Dimensions weighing surface	80 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	stainless steel
Material draught shield	plastic, glass
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Transport safety lock - bolt torque	0,1 Nm

Functions

PreTare function	✓
Sum memory function	✓
Recipe/summing level	Rez A (Net total)
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓

KERN EWJ 300-3



High-quality precision balance with automatic internal adjustment

Capacity - Display	✓
Counting function	✓
Counting resolution (laboratory conditions)	150.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	2 mg
Smallest piece weight when piece counting - normal conditions	20 mg
Reference quantity	5, 10, 20, 50, free, Input
Hold function	✓
IP protection - display	no IP protection
IP protection - load cell	IP65
Statistic function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	2 min
	1 min
	30 min
	60 min
	30 sec
Tare function	manual (multi)
Number of keys for operation	7

Interface

Interfaces	RS-232 standard Bluetooth BTC (v2.0) (optional, factory) Bluetooth BLE (v4.0) (optional, factory) USB-Device
------------	---

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,5 mm
Battery / accumulator type	Li-Ion
Battery connection	2-pole tub connector
Rechargeable battery operating time - backlight on	32 h

Rechargeable battery operating time - backlight off	57 h
Rechargeable battery charging time	6,5 h
Rechargeable battery optional	Rchrg. battery optional - intern

Environmental conditions

Ambient temperature [Min]	10 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration	963-127
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	410×295×275 mm
Shipping method	Parcel service
Net weight approx.	2,2 kg
Gross weight approx.	3,8 kg
Shipping weight	6,7 kg

Product information

GTIN/EAN number	4045761475373
REACH classification	no prohibited substances


KERN EWJ 300-3



High-quality precision balance with automatic internal adjustment

Pictograms

STANDARD



OPTION



FACTORY

