

KERN KDE-T

Display device

KERN



Category	
Brand	KERN
Product category	Spare part
Product group	Spare part

Measuring System	
Number of weighing ranges	2
Terminal resolution (not verifiable)	20.000
Adjustment options	Adjusting with external weight
Linearisation in dots	4
Units	kg
	g
	lb
	oz
Default unit	kg

Display	
Display type	LCD
Display type	LCD with backlight
Display backlight	✓
Display digit height	25 mm

Construction	
Dimension housing (W×D×H)	225×110×45 mm
Material display housing	plastic

Functions	
PreTare function	✓
Recipe/summing level	Rez A (Net total)
Percentage determination	✓
Function for averaging under unstable weighing conditions	✓
Time display	✓

Counting function	✓
Reference quantity	5, 10, 20, 25, 50
Hold function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Auto-off interval(s) in mains power mode	off
Tare function	manual (multi)

Interface	
Interfaces	RS-232 standard

Power Supply	
Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH
Plug-in power supply / adapter for countries - optional	EURO
	UK
	US
	CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	15 V, 500 mA
Battery	9 V block
Battery operating time	24 h
Rechargeable battery	NDE-A02
Rechargeable battery operating time - backlight on	10 h
Rechargeable battery operating time - backlight off	15 h
Rechargeable battery charging time	10 h
Rechargeable battery optional	Rchrg. battery optional - intern

Environmental conditions	
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval	
CE mark	✓

KERN KDE-T



Display device

Services (optional)

Article number for adjustment at the location of installation	auf Anfrage on request
---	--------------------------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	205×270×70 mm
Shipping method	Parcel service
Net weight approx.	0,70 kg
Gross weight approx.	1,00 kg
Shipping weight	1 kg

Product information

GTIN/EAN number	4045761133242
-----------------	---------------

Pictograms