

# Datasheet

Item no. 1576668, 1576669, 1576670, 1576671, 1576672, 1576673, 1576674

**Aufbau:**

5 A – 40 A Glasrohr, durchsichtig

## Bemessungswerte / Ratings

Art.- No.	Strom Current	Spannung Voltage	Spannungsfall Voltage drop [mV] max.	Spannungsfall Voltage drop [mV] <b>max ist.</b>	Max. Verlustleistung Max. power dissipation [W]	Schmelzintegral Melting integral [A <sup>2</sup> S]
TC-140024	5A		n.g.			
TC-140027	10A		n.g.			
TC-140029	15A		n.g.	222		
TC-140031	20A		n.g.			
TC-140032	25A		n.g.			
TC-140033	30A		n.g.			
TC-140035	40A		n.g.			

## Schmelzzeit-Grenzwert

Bemessungsstrom Rated current	1,35 I <sub>rat</sub>		1,5		4 I <sub>rat</sub>		10 I <sub>rat</sub>	
	min.	max.	min.	max.	min.	max.	min.	max.
5A - 40A		3600 s		30 s				