

Datasheet

Item no. TC-00180321203, TC-00180615203, TC-00180940203, TC-00181208203
 TC-00181215203, TC-00181440203, TC-00181640203, TC-00181940203

V1_0717_02_DT

Gluehlampe E5.5 - 4x15mm



	TC-00180321203	TC-00180615203	TC-00180940203	TC-00181208203	TC-00181215203	TC-00181440203	TC-00181640203	TC-00181940203
Betriebsspannung DC	3,5 V DC	6 V DC	9 V DC	12 V DC		14 V DC	16 V DC	19 V DC
Typ. Betriebsstrom	200 mA	150 mA	40 mA	80 mA	150 mA	40 mA		
Typ. Leistungsaufnahme	0,7 W	0,9 W	0,36 W	0,96 W	1,8 W	0,56 W	0,64 W	0,76 W
Socketart	E5,5							
Ausführung Glas	klar							
Wendelform	C-2R							
Höhe	15 mm							
Durchmesser	4 mm							

MAßE

