



**Series/Type**

: Cylindrical type lithium batteries (BR series)

**Parts no**

: BR-2/3A

## Specification

Item	Performance characteristics
Nominal Voltage (V)	3
Nominal Capacity (mAh)	1200
Continuous Standard Drain (mA)	2.5
Diameter (mm)	17
Thickness (mm)	-
Height (mm)	33.5
Approx. Weight (g)	13.5
JIS	-
IEC	BR17335