



Discover more details and matching accessories online!

Compact pocket-sized material thickness gauge

- Features**

 - External measuring head for difficult-to-access measuring points
 - Selectable measuring units: mm, inch
 - Data interface RS-232, included
 - AUTO-OFF-function to preserve the battery
 - Base plate for adjustment included
 - Scope of delivery: Operating instructions, batteries, external measuring head (ø 8 mm) and ultrasound contact gel
 - **1** Delivered in a robust carrying case
- Technical data**

 - Measuring precision: 0,5 % of [Max] + 0,1 mm
 - Overall dimensions W×D×H 30×65×120 mm
 - Battery operation, batteries standard (4×1.5 V AAA)
 - Net weight approx. 0,20 kg

STANDARD



OPTION



Model	Measuring range	Readout	Sensor	Sound velocity	Option
					Factory calibration certificate
SAUTER	mm	[d] mm		m/sec	KERN
TD 225-0.1US	1,2 – 225	0,1	5 MHz ø 8 mm	1000 – 9999	961-113