LIEBHERR

EU declaration of conformity regarding energy consumption according to (EU) 2019/2019

Energy Label (EU) 2019/2016

Applied standard EN 62552:2020

Product information sheet

Supplier's name or trade mark	Liebherr
Supplier's address	Liebherr-Hausgeräte GmbH Memminger Straße 77-79 88416 Ochsenhausen Germany
Model identifier	GP 1213_992705851

Electrical data

Voltage	220-240 V ~
Frequency	50 Hz
Connection rating	1.3 A

Type of refrigerating appliance

Low-noise appliance	no	Design type	freestanding
Wine storage appliance	no	Other refrigerating appliance	yes

General product parameters

Parameter		Value	Parameter	Value
Overall dimensions (millimetre)	Height	851	Total volume (dm³ or l)	97
	Width	553		
	Depth	624		
EEI		100	Energy efficiency class	E
Airborne acoustical noise emissions (dB(A) re 1 pW)		39	Airborne acoustical noise emission class	C
Annual energy consumption (kWh/a)		169.93	Climate class	extended temperate, temperate, subtropical, tropical
Minimum ambient temperature (°C), for which the refrigerating appliance is suitable		10		
Maximum ambient temperature (°C), for which the refrigerating appliance is suitable		43	Winter setting	no

Compartment Parameters

Compartment type		Compartment parameters and values			
		Compartment Volume (dm³ or l)	**Recommended temperature setting for optimised food storage (°C)**	**Freezing capacity (kg/24 h)**	**Defrosting type** (auto-defrost = A, manual defrost = M)
Pantry	no	-	-	-	-
Wine storage	no	-	-	-	-
Cellar	no	-	-	-	-
Fresh food	no	-	-	-	-
Chill	no	-	-	-	-
0-star or ice-making	no	-	-	-	-
1-star	no	-	-	-	-
2-star	no	-	-	-	-
3-star	no	-	-	-	-
4-star	yes	97.9	-18	6.00	M
2-star section	no	-	-	-	-
Variable temperature compartment	no	-	-	-	-

For 4-star compartments

Fast freeze facility	yes

Light source parameters

Type of light source n.a.	Lighting technology used	n.a.
	Non-directional or directional	n.a.
	Mains or non-mains	n.a.
	Connected light source (CLS)	n.a.
	Colour-tuneable light source	n.a.
	Envelope	n.a.
	High luminance light source	n.a.
	Anti-glare shield	n.a.
	Dimmable	n.a.
	Energy efficiency class	n.a.

Minimum duration of the guarantee offered by the manufacturer: 24 month

Additional information: -

Weblink to the manufacturer's website, where the information in point 4(a) Annex of Commission Regulation (EU) 2019/2019 (4) (2) is found: https://home.liebherr.com/

The energy consumption was confirmed by measurements according to EN 62552:2020.