

**Tragschienen
TS 27X12.5M/ST/F.ZN**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Produktbild**Allgemeine Bestelldaten**

Typ	TS 27X12.5M/ST/F.ZN
Best.-Nr.	1802690000
Ausführung	Tragschienen, Tragschiene, DIN EN 60715, Stahl
GTIN (EAN)	4032248257201
VPE	2 m

Tragschienen TS 27X12.5M/ST/F.ZN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Abmessungen und Gewichte

Breite	27 mm	Breite (inch)	1,063 inch
Höhe	12,5 mm	Höhe (inch)	0,492 inch
Tiefe	12,5 mm	Tiefe (inch)	0,492 inch
Nettogewicht	50 g		

Tragschiene

Stärke	2 mm
--------	------

Klassifikationen

ETIM 3.0	EC001285	ETIM 4.0	EC001285
ETIM 5.0	EC001285	ETIM 6.0	EC001285
UNSPSC	30-21-18-01	eClass 5.1	27-14-06-04
eClass 6.2	27-14-11-43	eClass 7.1	27-14-11-43
eClass 8.1	27-14-11-43	eClass 9.0	27-40-06-02
eClass 9.1	27-40-06-02		

Zulassungen

ROHS	Konform
------	---------

Downloads

Broschüre/Katalog	CAT 1 TERM 16/17 EN
Engineering-Daten	EPLAN, WSCAD
Engineering-Daten	STEP