

## AFG31000 Series Arbitrary/Function Generator

Model	Analog Channels	Output Frequency	Output Amplitude into 50 $\Omega$	Waveform Memory Size	Sample Rate	Conrad Bestellnr.:
AFG31021	1	25 MHz	1 mVpp to 10 Vpp	16 MSa/ch	250 MS/s	<b>1785552</b>
AFG31022	2	25 MHz	1 mVpp to 10 Vpp	16 MSa/ch	250 MS/s	<b>1785553</b>
AFG31051	1	50 MHz	1 mVpp to 10 Vpp	16 MSa/ch	500 MS/s	<b>1785554</b>
AFG31052	2	50 MHz	1 mVpp to 10 Vpp	16 MSa/ch	500 MS/s	<b>1785555</b>
AFG31101	1	100 MHz	1 mVpp to 10 Vpp	16 MSa/ch	1 GS/s	<b>1785556</b>
AFG31102	2	100 MHz	1 mVpp to 10 Vpp	16 MSa/ch	1 GS/s	<b>1785557</b>
AFG31151	1	150 MHz	1 mVpp to 5 Vpp	16 MSa/ch	2 GS/s	
AFG31152	2	150 MHz	1 mVpp to 5 Vpp	16 MSa/ch	2 GS/s	
AFG31251	1	250 MHz	1 mVpp to 5 Vpp	16 MSa/ch	2 GS/s	
AFG31252	2	250 MHz	1 mVpp to 5 Vpp	16 MSa/ch	2 GS/s	

Erhältlich bei:

