

Technische Daten

TUNER	DAB / DAB+	Channel Block	5A - 13F
	FM	Frequency (MHz)	87.5 - 108
		RDS / RBDS	PS / PTY / CT / RT
	WiFi	IEEE 802.11 b / g (GHz)	2.4GHz / 5GHz
	Ethernet	IEEE 802.3	V
		Internet Radio (iRadio)	vTuner
		Media Player (mPlayer)	UPnP
TUNING		Memory Presets	30 (10 iRadio, 10 FM and 10 DAB)
MEDIA	CD	CD / CD-R / CD-RW	CD / MP3 playback
	SD		V
	USB Playback		V
	Aux - in		V
	Bluetooth		V
BLUETOOTH		NFC	V
		AVRCP	V
		APT-X	V
AUDIO DECODING		Internet Radio (iRadio)	MP3 / WMA / Real Audio
		Media Player (mPlayer)	MP3 / AAC / WMA
		CD / SD / USB	CD
CLOCK	Real time	Time	V
	Alarm	Tuner / iRadio / Buzzer	V
	Sleep		V
	Snooze		V
FEATURE		Stereo	V
		Record - SD Card / USB Stick	V
		Spotify	V
AUDIO	Sound Effect	Treble / Bass Control	V
	EQ	EQ (Sound Effect Selection)	V
OUTPUT POWER		Output Power	7W*2
		Earphones Output Power	3mW*2
		Class D Amplifier	V
I/O SOCKET		Power	AC- in
		Aux - in	V

	Line - out	V
	SPDIF out	V
	Earphones	V
	SD	V
	USB	V
POWER SUPPLY	Ext.Antenna	WiFi / F type (DAB / FM)
ACCESSORIES	Ethernet	V
	Mains Power Supply	AC 100-240V
DIMENSIONS	AC Cord	V
	Remote Control	V (Remote + APP)
	Width (mm/inch)	356 / 14.02
	Height (mm/inch)	121.5 / 4.78
	Depth (mm/inch)	252 / 9.92
	Weight (g & lb. oz)	4100 / 9lb. 0.6oz