



29W

VT-6262 29W LED PANEL-62x62CM COLORCODE:4000K HIGH LUMEN

Lumens 3480	Beam Angle 120	Dimensions 620x620x15.5mm
-----------------------	--------------------------	-------------------------------------

Day White
SKU:6471

2 YEARS
WARRANTY

SENSOR
COMPATIBLE



Technical Information

Instant Start:	0-100% lt1 Sec	LED Chip Type:	SMD
Watts:	29	IP Rating:	IP20
Lumens:	3480	Dimmable:	No
Shape:	Square	Warranty (Years):	2
On/Off Cycles::	>20000	PF:	>0.9
Beam Angle:	120	CRI:	>80
Unit Color:	White	Operation Temperature:	-20°C to +45°C
Body Type:	Aluminium + PMMA	Input Power:	AC:220-240V,50/60Hz
Long life:	30,000 Hours	Sensor Compatibility:	Yes

Features

- ✓ Compare with incandescent, it can save over 80% electric cost
- ✓ Contemporary & Elegant Design
- ✓ Higher Light Transmission Rate
- ✓ Easy to install - Plug and play version
- ✓ Dimmable options available
- ✓ High quality power driver ensures reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Range of Sizes to suit different workspaces
- ✓ Instant Start - 0-100% in
- ✓ No flickering, No U.V Radiation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	2.891445
Unit CBM	0.010725

Listing Details

EAN Code	3800157641012
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	6
---------------------------------	---

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES