


KERN DAB 200-2

KERN

Particularly user-friendly moisture analyser with high-quality halogen quartz glass heater - ideal for recurring rapid tests



Category

Brand	KERN
Product category	Laboratory balance
Product group	Moisture analyser
Product family	DAB

Measuring System

Reproducibility weight of sample 2 g	1,5%
Weighing system	Strain gauge
Weighing capacity [Max]	200 g
Readability [d]	0,01 g
Reproducibility	0,01 g
Linearity	± 0,03 g
Resolution	20.000
Tare range	200 g
Adjustment options	Adjusting with external weight
Recommended adjusting weight	200 g (F2)
Possible calibration points	200 g
Stabilization time	3 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	0,05 g
Load cell connection	4-wire
Units (if device is conformity assessed)	g
Temperature increment	1 °C
USP Minimum weight of sample (k = 2, U = 0.1%)	20 g
Construction type of the scale	Single-range balance
Units	g % Humidity % Dry mass

Temperature [Min] (°C)	40 °C
Temperature [Max] (°C)	199 °C
Reproducibility weight of sample 10 g	0,3%
Maximum creep (15 minutes)	40 mg
Maximum creep (30 minutes)	80 mg
Sample - Moisture content	20% - 100%
Sample - Dry content	100% - 20%
Default unit	g
Readability moisture [d] (%)	0,05%

Display

Display type	graphic
Display backlight	✓
Display screen size	5.4"
Display segments	7
Display digit height - smallest digit	6 mm
Display digit height	14 mm

Construction

Dimensions completely mounted (W×D×H)	240×365×180 mm
Dimensions weighing surface (Ø)	92 mm
Dimensions weighing surface	92 mm
Material housing	cast aluminium, plastic
Material weighing plate	aluminium sample plates
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Heat generation capacity (W)	400

Functions

Drying modes	Standard drying Rapid drying Gentle drying
Memory - number of drying programs	15
Switch-off criteria	time controlled automatic manual
Memory function	✓
Memory - number of results	5
Memory - number of sample (descriptions)	5
Auto-off interval(s) in mains power mode	off
Tare function	manual (multi)
Number of keys for operation	9

KERN DAB 200-2



Particularly user-friendly moisture analyser with high-quality halogen quartz glass heater - ideal for recurring rapid tests

Interface

Interfaces	RS-232 standard
------------	-----------------

Power Supply

Supplied power supply	Power supply unit
Power supply type	Built-in power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	UK
Input voltage power supply / power [Max]	230 V AC, 50 Hz
Power supply cable removable	removable
Input voltage device / power [Max]	230 V AC, 50 Hz
Power socket for mains adapter	Power supply cable
Battery	no battery

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	5 %
Humidity of environment [Max]	80 %

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration	963-127
Article number for factory calibration (temperature)	964-305
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	490×350×360 mm
Shipping method	Parcel service
Net weight approx.	5,0 kg
Gross weight approx.	8 kg
Shipping weight	12,3 kg

Product information

GTIN/EAN number	4045761213029
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

