

KERN EOB 60K20

KERN

Allround parcel scale with robust stainless steel weighing plate



Category	
Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	EOB

Measuring System	
Weighing system	Strain gauge
Weighing capacity [Max]	60 kg
Readability [d]	0,02 kg
Reproducibility	0,02 kg
Linearity	± 0,04 kg
Resolution	3.000
Tare range	60 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	40 kg (M2)
Possible calibration points	40 kg
Stabilization time	3 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	0,06 kg
Construction type of the scale	Single-range balance
Units	kg lb PCS
Maximum creep (15 minutes)	80 g
Maximum creep (30 minutes)	160 g
Default unit	kg

Display	
Display type	LCD
Display backlight	✓

Display screen size	115×40 mm
Display digit height	25 mm

Construction	
Dimension display device (W×D×H)	235×114×51 mm
Dimensions weighing surface (W×D)	315×305 mm
Dimensions weighing surface	315×305 mm
Dimensions weighing platform (W×D×H)	315×305×57 mm
Material housing	plastic
Material weighing plate	stainless steel
Material display housing	plastic
Wall mount	✓
Display device cable length	1,8 m

Functions	
Underfloor weighing	None
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Hold function	✓
IP protection - complete device	-
IP protection - display	no IP protection
IP protection - platform	no IP protection
IP protection - load cell	no IP protection
Auto-off interval(s) in battery mode/rechargeable battery mode	off 1 min - 99 min
Auto-off interval(s) in mains power mode	off 1 min - 99 min
Tare function	manual (multi)
Number of keys for operation	4

Power Supply	
Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	9 V, 100 mA

KERN EOB 60K20



Allround parcel scale with robust stainless steel weighing plate

Power socket for mains adapter	Hollow plug, inside minus, Ø outside 5,5 mm, Ø inside 2,5 mm, long 10 mm
Battery / accumulator type	Alkali(-Manganese)
Battery	4×1.5 V AA
Battery connection	Pad + Spring
Battery operating time	60 h

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %

Approval

CE mark	✓
---------	---

Services (optional)

Article number for adjustment at the location of installation	961-249
Article number for DAkkS calibration	963-129
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	370×365×140 mm
Shipping method	Parcel service
Net weight approx.	3,8 kg
Gross weight approx.	5,0 kg
Shipping weight	4,93 kg

Product information

GTIN/EAN number	4045761192126
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

