

GOXTREME[®]

VISION 4K

4K
24FPS



RESOLUTIONS

Video	fps
4K	24
2.5K	30
1080p	60 / 30
720p	120 / 60 / 30
Photo	16M / 14M* / 12M / 10M / 8M / 5M / 3M / VGA

DISPLAY

LCD display	2.0"/5cm
-------------	----------

FEATURES

Sensor	12MP
Waterproof case	Up to 30m
Microphone / speaker	Built-in
Wide angle	170°
Field of view	Wide / Medium / Narrow
Motion detection	Yes
Slow motion	720p 120 / VGA 240
Time lapse video	1s / 2s / 5s / 10s / 30s / 60s
Time lapse photo	3s / 5s / 10s photo intervals
Burst rate	3shots/s / 5shots/s / 10shots/s
Auto photo shots	Single / 2s timer / 5s timer / 10s timer / 20s timer
White balance	Auto / Daylight / Cloudy / Tungsten Light / Fluorescent
SAR	17dbm
EIRP	0.181W
Frequency	2412.0-2462.0
File format	MOV, JPG
Interface	HDMI, USB 2.0 Micro
Working temperature	-5°C to +45°C
Power source	Exchangable 1050mAh lithium battery
Dimensions	59 x 41 x 29 mm

EXTERNAL MEMORY (not included)

Requirements	Compatible with microSD cards up to max. 64GB U3 class10 cards required (or faster)
--------------	--

WIFI CONNECTION

WiFi function	Built-in
App	<p>"OKCAM PLUS" for Android or iOS</p> <p>Download the app from the App Store or Google Play to control your action cam by your phone or tablet via WiFi.</p> <p>Please note that it is not possible to wirelessly playback or transfer files exceeding 1080p resolution using the app. Files using any resolution higher than 1080p can only be accessed via computer. Due to certain WiFi restrictions it is not possible to transfer videos of 2.5K or 4K resolution.</p>



*by interpolation



MOUNTS INCLUDED



Waterproof case, hollow back door, bike mount, frame mount with clip, long/short base, tripod adapter, monopod adapter, helmet base, long/short joint adapters, battery, straps, lens cloth, USB cable, manual