



According to ISO 2768-m

Measuring DIM=L	Tolerances
0.5<L<=3.0mm	±0.1mm
3.0<L<=6.0 mm	±0.1mm
6.0<L<=30.0 mm	±0.2mm
30.0<L<=120.0 mm	±0.3mm
120.0<L<=400.0 mm	±0.5mm
400.0<L<=1000.0 mm	±0.8mm

STOCK NO.	MATERIAL	BASE-COLOR	COVER-COLOR
G279MF	PDLYCARBONATE UL94-HB	LIGHT GRAY(RAL7035)	LIGHT GRAY(RAL7035)
G279CMF	PDLYCARBONATE UL94-HB	LIGHT GRAY(RAL7035)	CLEAR
G387MF	ABS UL94-HB	DARK GRAY(RAL7000)	DARK GRAY(RAL7000)

宜文實業有限公司 GAINIA INDUSTRIES LTD.	繪圖	DRA'D BY	日期	DATE	材質	MATE.	圖名	TITLE:	圖號	DWG NO:	版本	REVISID:	宜文實業有限公司 GAINIA INDUSTRIES LTD.	繪圖	DRA'D BY	日期	DATE	材質	MATE.	圖名	TITLE:	圖號	DWG NO:	版本	REVISID:
	JACKY	2013/02/08	PC/ABS	G279MF,G387MF		A	JACKY	2013/02/08	PC/ABS	G279MF,G387MF		A													