


OMARI 5-SPOT | SPOTS | WHITE

2112203001

nordlux®



Voltage (V): 230 Volt
IP degree if the fixture includes
two types of IP degree: IP20
Class (Class I, Class II, Class III):
Class 2 (Double isolated)
Lampholder type (eg, E27/E14,
etc): LED Module

Primary material: Metal
Is the cable replaceable: False

Color: White
Height (cm): 12
Width (cm): 3.5
Shade Diameter (cm): 3
Base Dimention (cm): 118
Lenght (cm): 118
Tilt Angle (°): 90
Turning Angle (°): 320

EAN: 5704924005374
TUN: 2148763
Item Number: 2112203001
Pcs Per Master Carton: 2

Sales Box Height (cm): 11
Sales Box Width(cm): 118.5
Sales Box Depth (cm): 4.5
Sales Box Volume m³ : 0.0059
Net weight of the luminaire (kg):
1.65

Useful Lumen (lm): 320
Color Temperature (K): 2700
Ra-value : 80
Lifetime (h): 25000
Spread Angle (°) (beam angle of
luminaire): 41
Candela (cd) (for directional
lamp only): 550
Energy Class: F

- Minimalist and streamlined design • 3-step dimming
- Adjustable lamp head for a directional light • Minimalist and streamlined design

Omari is a series of spots focusing on light, clean and simple Nordic lines. This minimalist and streamlined ceiling light with five spots fits perfectly into most interior designs. MoodMaker (three-step dimming) on the wall switch makes it easy for you to create just the right cosy ambience.