

KERN ORA 3AB

Refractive index measurement for laboratories and the industry

KERN

Category

Brand	Optics
Product category	Refractometer
Product group	Analogue refractometer
Product family	ORA-AL

Measuring System

Measurement temperature [Min] (°C)	10 °C
Measurement temperature [Max] (°C)	30 °C
Measuring method	Light refraction
Measuring range Brix [Min]	0 %

Scales	Brix Stammwürze (Bier) 0 % - 32 %
Measuring ranges	1,000 SG Wort - 1,130 SG Wort

Readabilities [d]	0,2 % 0,001 SG Wort
-------------------	------------------------

Readout Brix	0,2 %
--------------	-------

Measuring range original hopped wort (specific gravity) [Min]	1,000
---	-------

Measuring range original hopped wort (specific gravity) [Max]	1,130
---	-------

Readout original hopped wort (specific gravity)	0,001
---	-------

Scale original hopped wort (specific gravity)	✓
---	---

Appropriate calibration liquid	0 % (distilled water)
--------------------------------	-----------------------

Measuring range Brix [Max]	32 %
----------------------------	------

Brix scale	✓
------------	---

Area of application	Beer
---------------------	------

Construction

Dimension (W×D×H)	198×40×40 mm
Refractometer type	Handheld refractometer
Scale - Display type	Analogue
Material prism	ZLaF3 lanthanum flint glass nd=1.85544

Functions

IP protection - complete device	-
---------------------------------	---

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Services (optional)

Article number for factory calibration	961-290
--	---------

Packing & Shipping

Dimensions transport container (W×D×H)	205×75×55 mm
Delivery time	1 d
Dimensions packaging (W×D×H)	215×94×65 mm
Shipping method	Parcel service
Net weight approx.	0,30 kg
Gross weight approx.	0,35 kg
Shipping weight	0,32 kg

Product information

GTIN/EAN number	4045761261051
REACH classification	no prohibited substances

Pictograms

STANDARD

