

## Elektro Starter 15cc - 62cc

### Specification:

Size:205mm\*124mm\*50mm

Package size:265mm\*165mm\*72mm

Net weight:780g

Gross weight:885g

Work voltage: DC 12V~17V

Work Battery: 3S~4S 2200mah (20c or Above 20cc) Lipo battery

Battery connector: XT60 Female plug

Starter rubber cap size:  $\Phi$ 36mm\*D24mm\*H30mm

### Feature:

Super High-Torque, Easy to start

Starts All models from 21-120 scales Methanol engine

Full Protection Hand-Guard for Extra Safety

Customized Solid state relay make it more durable

3-4S Lipo battery plug in and start

### Requirements:

One 12~17v 2200mah 20c or higher capacity Lipo battery

Notes:

1. When the starter overheating please stop using it until it is cooled
2. Please remove the battery when the starter is not in use
3. Please add a Low-voltage alarm to the Lipo battery when the starter is in use

Pichler Modellbau GmbH

Lauterbachstraße 19

84307 Eggenfelden

GERMANY