




Hauptmerkmale

Baureihe	EcoStruxure Operator Terminal Expert
Produkt- oder Komponententyp	Lizenz
Format	Digital
Softwaretyp	Professional
Lizenztyp	Arbeitsplatz-Lizenz
Variante	Buildtime
Software-Version	V3.5
Operating system requirement	Windows 10 64 bit
Systemanforderungen	8 GB RAM 30 GB hard-drive space
Benutzersprache	Englisch Italienisch Chinesisch Spanisch Französisch Deutsch Portugiesisch Koreanisch

Zusatzmerkmale

Kategorie der Lizenz	Permanent
Kommunikationsprotokoll	CANopen-Slave Couzet Automation millenium 3 FBD Emerson Industrial Automation Modbus SIO master Control Techniques Modbus SIO master Emerson Process Management ROC Plus Ethernet Emerson Process Management ROC SIO HTTP IPsec Mitsubishi A series Ethernet Mitsubishi FX series CPU direct Mitsubishi FX series Ethernet Mitsubishi iQ-R/F series Ethernet SLMP client Mitsubishi Q series CPU direkt Mitsubishi Q series QnU CPU Ethernet Mitsubishi Q/QnA series serial Modbus Organization Modbus SIO ASCII master Modbus Organization Modbus SIO master Modbus Organization Modbus SIO slave Modbus Organization Modbus TCP Master Modbus Organization Modbus TCP slave Omron CS/CJ/CP series host link Omron CS/CJ/CP/NX series Ethernet Omron CS/CJ/NJ/NX series Ethernet/IP OPC UA server Profibus DP slave Rockwell Automation EtherNet/IP Rockwell Automation DF1 Rockwell Automation DH485 Schneider Electric Modbus SIO master Schneider Electric Modbus TCP Master Schneider Electric Modbus TCP Master via USB Schneider Electric Machine expert network Schneider Electric PacDrive Schneider Electric Uni-Telway Schneider Electric Zelio Logic Siemens Simatic S7 Ethernet Siemens Simatic S7 MPI direkt Siemens TIA portal Ethernet websocket
Vorhergehende Software-Version	V3.4
Funktion der Software	Professional screen design Simulation Alarms and events Blocky script Convertors Dockable windows interface environment Export with CSV and tab delimiter Import with CSV and tab format Data and operation logging Multi language development Multi language tables Object binding and properties Target binding and properties Project transfer (Ethernet, filesystem, USB cable) Recipes Screens (contents and folders) Security (levels, project, users) Project and application settings System keypad Text script Color themes Variable (arrays, binding, properties, structures) Online and integrated help system OPC UA Server Web server API
Kompatible Produktfamilie	Harmony GTU Harmony GTUX Harmony ST6 Harmony STM6 Harmony STO7 Harmony iPC
Hosting-Option	Ortsgebundene
Lizenzgröße	Entity (100 station)

Processor requirement	Intel core i3 8th generation Intel core i5 8th generation
Auflösung der Anzeige	1280 x 720 pixels HD

Verpackungseinheiten

VPE 1 Art	PCE
VPE 1 Menge	1
VPE 1 Höhe	1,0 cm
VPE 1 Breite	1,0 cm
VPE 1 Länge	2,0 cm
VPE 1 Gewicht	2,0 g

Vertragliche Gewährleistung

Garantie	18 Monate
----------	-----------