









GS1 250...315 A



(3x250A) GS1-AF 43
(4x250A) GS1-AF 44



GS1-AN 11 : 1 0 + F
GS1-AN 22 : 2 0 + F
GS1-AN 33 : 3 0 + F
GS1-AN 44 : 4 0 + F



O + F (NO + NC) → 2 F (2NO)
→ 2 O (2NC)

