

LED Zubehör
LED accessoriesSensor Kabel, 10 m, M8 Buchse, 5-polig/
offene Leitungsenden

Artikel-Nr.:	200100-25
EAN:	4260556626048

Bestell-Nr.:	200100-25
Modell:	LED2WORK Sensor Kabel für 24V DC
Bauform:	Sensor Kabel, PUR, schwarz
Geeignet für:	TUBELED_25 RGB-W (nicht TUBELED_25)
Anzahl:	1
Länge Kabel:	10 m
Kabelenden:	offene Enden, 5 Litzen/ M8 Buchse, gerade
Polzahl:	5
Material Kabel:	PUR
Befestigung an Leuchte:	Steckverbinder M8 Buchse, gerade
Gewicht:	200 g
Bruttogewicht:	200 g

Litzenfarben auf dem Bild können zum aktuellen Originalprodukt abweichen.



Sensor cable, 10 m (32,81 ft), M8 socket, 5-pole/ open cable ends

Item number:	200100-25
EAN:	4260556626048

Order number:	200100-25
Model:	LED2WORK sensor cable for 24V DC
Type:	sensor cable, PUR, black
Suitable for:	TUBELED_25 RGB-W (not TUBELED_25)
Quantity:	1
Lenght of cable:	10 m (32,81 ft)
Cable ends:	open ends, 5 cores / M8 socket, straight
Number of contacts:	5
Material cable:	PUR
Connection:	connector M8 socket, straight
Weight (net):	200 g (~7 oz)
Gross weight:	200 g (~7 oz)

The wire colours in the illustration may differ from the current original product.