

KODAK PIXPRO WPZ2

DIGITAL CAMERA



WPZ2 RUGGED CAMERA

The KODAK PIXPRO WPZ2 Digital Camera is the perfect companion to get wet. Shockproof, dustproof, and adventure ready, the WPZ2 was built to take on the go and be used in, on and under the water. With a host of scene modes and 1080p HD video to help you capture your best shots, the WPZ2 is not going to miss a beat. Built-in Wi-Fi® allows you to connect the WPZ2 to your iOS™/ANDROID™ device and share your outdoor adventures with friends or on social media. KODAK PIXPRO Digital Cameras – Tell your story.

FEATURES:

- 16 MP CMOS Sensor
- 4x Optical Zoom
- 1080p HD Video
- 15m Waterproof
- 2m Shockproof/Dustproof
- Wi-Fi® Connection
- Li-ion Battery



PIXPRO Remote Viewer App



4X
Optical
Zoom

16MP
CMOS

1080p
Full HD

15m/49FT
Waterproof

2m/6FT
Shockproof

Lithium-ion
Battery



Available
Colors:

- Yellow
- Red
- Blue
- White
- Orange



KODAK PIXPRO WPZ2

DIGITAL CAMERA

SPECIFICATIONS	WPZ2
Effective Image Sensor Pixels	16.35 Megapixels
Total Image Sensor Pixels	16.76 Megapixels [1/2.3" BSI CMOS]
Lens	
Focal Length	4.9 mm (Wide) — 19.6 mm (Tele)
[35mm film equivalent]	[27 mm (Wide) — 108 mm (Tele)]
F number	F3.0 (Wide) — F6.6 (Tele)
Lens Construction	7 groups 7 elements
Optical Zoom	4x
Focusing Range	Normal: (Wide) 60cm — ∞(Tele) 100 — ∞ Macro: 5cm — ∞(Wide Only)
Autofocus System	TTL Autofocus
Anti-Handshake	Digital Image Stabilization
Digital Zoom	6x Digital Zoom (Combined Zoom: 24x)
Number of Recording Pixels	
Still Image	(4:3) 16MP: 4608x3456, 10MP: 3648x2736, 5MP: 2592x1944, 3MP: 2048x1536, 0.3MP: 640x480, (3:2) 14MP: 4608x3072, (16:9) 12MP: 4608x2592, 2MP: 1920x1080
Movie	1920x1080: 30fps, 1280x720: 60 fps / 30fps, 640x480: 30fps; High Speed Movie 640x480: 120fps
Image Compression	Best, Fine, Normal
DCF, DPOF (Ver1.1) Support	Yes
File Format	
Still Image	Exif 2.3 (JPEG)
Movie	MOV [Image: H. 264; Audio: Linear PCM (Monaural)]
Shooting Modes	Auto, P, M, Wi-Fi, SCN, Movie, Underwater, Panorama, Children, Portrait, Night Portrait, Landscape, Sport, Sunset, Fireworks, Snow, Party, Beach, Night Landscape, Glass, Panning Shot, Indoor, Leaf, Museum, Imaging Stabilization
Detection Features	Face, Smile, Blink
Waterproof	Up to 15m / 49ft
Shockproof	Up to 2m / 6ft
Dustproof	Equivalent to JIS/IEC (IP6X)
Red-Eye Removal	Yes
HDR (High Dynamic Range)	Yes (Post-Processing)
Scan Panorama	Up to 360°
LCD Display	2.7 inch (230K Pixels)
ISO Sensitivity	Auto, ISO 100/200/400/800/1600/3200
AF Method	Single AF, Multi-AF (TTL 25-point), Face-Detection
Exposure Metering Method	Artificial Intelligence AE (AiAE), Center-Weighted Average, Spot (Fixed to Center of Frame), Face AE
Exposure Control Method	Program AE (AE-Lock Available)
Exposure Compensation	+/- 3EV in 1/3 Step Increments
Shutter Speed	1/2000 - 4 Seconds (Manual: 30 Seconds)
Burst Mode	Approx. 6fps (Full Resolution)
Playback Modes	Single, Index (9/16 Thumbnails), Slide Show, Date, Burst Shooting, Zoom (Approx. x2 ~ x8)
White Balance Control	Auto (AWB), Daylight, Cloudy, Fluorescent, Fluorescent CWF, Incandescent, Manual, Underwater, Color Temperature, Setting (1900K ~ 10000K)
Flash	
Flash Method	Internal
Flash Modes	Auto, Red-Eye Reduction, Fill Flash, Slow Synchro, Red-Eye Reduction + Slow Synchro, Force Off
Shooting Range	(Wide) Approx. 0.3m ~ 5.2m (ISO800) (Tele) Approx. 1.0m ~ 2.4m (ISO800)
Recycle Time	6 seconds or less
Recording Media	Internal Memory: Approx. 8MB, microSD/ microSDHC Card (Up to 32GB Support/Class 4 or Higher) [MMC Card Not Supported]
Other Features	Wi-Fi (802.11 b/g/n), Remote Control (via iOS™/ANDROID™ Device), Multi-Language Support (26 Languages)
Jacks	USB 2.0 (Micro 5 pin USB)
Power	Rechargeable Li-ion Battery (LB-015), 3.7V 700mAh, In-Camera Charging
Shooting Capability (Battery Performance)	Approx.200 Shots (Based on CIPA Standards), Approx. 1h 10min for Video (@1080p/30fps)
Operation Environment	Temperature: 32° ~ 104°F / 0° ~ 40°C, Humidity: 0 ~ 90%
Dimensions (WxHxD)	Approx. 103.2 × 66.7 × 52.4 mm / 4.06 x 2.62 x 2.06 in. (Based on CIPA Standards)
Weight	Approx. 6.21 oz. / 176g (Body Only)
Supplied Accessories	Rechargeable Li-ion Battery, Wrist Strap, Quick Start Guide, USB cable, Warranty Card, and Service Card

JK Imaging Ltd.

17239 So. Main Street, Gardena, CA 90248 (888) 978-0806

© 2024 JK Imaging, Ltd. The Kodak trademark, logo and trade dress are used under license from Eastman Kodak Company.

All information contained in this document is subject to change without notice. Document Number/Sequence: U.DIS.0061.0224.en.08

To learn more about KODAK PIXPRO Digital Cameras:
visit: kodakpixpro.com

