

Product fiche

Delegated Regulation (EU) 626/2011

Supplier name or trademark	Be COOL
Model identifier	BC14KL2402FW
Indoor Model Identifier(s)	BC14KL2402FW
Outdoor Model Identifier	
Inside sound power levels (Cooling mode)	65 dB
Inside sound power levels (Heating mode)	65 dB
Outside sound power levels (Cooling mode)	- dB
Outside sound power levels (Heating mode)	- dB
Refrigerant Name	R290
Refrigerant GWP	3
<p>Refrigerant leakage contributes to climate change. Refrigerant with lower global warming potential (GWP) would contribute less to global warming than a refrigerant with higher GWP, if leaked to the atmosphere. This appliance contains a refrigerant fluid with a GWP equal to 3. This means that if 1 kg of this refrigerant fluid would be leaked to the atmosphere, the impact on global warming would be 3 times higher than 1 kg of CO₂, over a period of 100 years. Never try to interfere with the refrigerant circuit yourself or disassemble the product yourself and always ask a professional.</p>	
Cooling Mode	
Energy Efficiency Ratio (EER)	2,7
Energy Efficiency Class	A
Hourly electricity consumption	Energy consumption 1,5 kWh per 60 minutes, based on standard test results. Actual energy consumption will depend on how the appliance is used and where it is located.
Cooling capacity	4,1 kW
Heating Mode	
Coefficient Of Performance (COP)	2,7
Energy Efficiency Class	A+
Hourly electricity consumption	Energy consumption 1,2 kWh per 60 minutes, based on standard test results. Actual energy consumption will depend on how the appliance is used and where it is located.
Heating capacity	3,2 kW