



Part Number : [190050015](#)
Product Description : InsulKrimp Fully Insulated Coupler, Female, for 12-10 AWG Wire, Mylar Tape
Series Number : 19005
Status : Active
Product Category : Quick Disconnects
Engineering Number : C-2265T



Documents & Resources

Drawings
[190050015_sd.pdf](#)

3D Models and Design Files
[190050015_stp.zip](#)

Specifications
[PS-19902-008-001.pdf](#)
[PS-19902-011-001.pdf](#)
[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19005
Description	InsulKrimp Fully Insulated Coupler, Female, for 12-10 AWG Wire, Mylar Tape
Product Name	InsulKrimp
Type	Quick Disconnect
UPC	800753030657

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Yellow
Flammability	94V-2
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	Nylon (PA)

Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.450/g
Orientation	Straight
Packaging Type	Adhesive Tape on Reel
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-65° to +105°C
Wire Insulation Diameter	6.99mm max.
Wire Size (AWG)	10, 12

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Use with Part(s)

Description	Part Number
InsulKrimp Fully Insulated Coupler, Male, for 12-10 AWG Wire, Box	<u>190040009</u>
InsulKrimp Fully Insulated Coupler, Male, for 12-10 AWG Wire	<u>190040012</u>

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880214</u>
Mini-Mac Applicator	<u>638850300</u>