



Part Number : [191210006](#)
Product Description : InsulKrimp Flanged
Spade Tongue Terminal for 22-18 AWG Wire,
Stud Size 6 (M3.5), Length 19.84mm, Mylar
Tape Carrier
Series Number : 19121
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : AA-215-06XT



Documents & Resources

Drawings
[191210006_sd.pdf](#)

3D Models and Design Files
[191210006_stp.zip](#)

Specifications
[PS-19902-009-001.pdf](#)
[PS-19902-011-001.pdf](#)
[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D

- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19121
Description	InsulKrimp Flanged Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 6 (M3.5), Length 19.84mm, Mylar Tape Carrier
Keyword	Spade Terminal, Spade Terminals
Product Name	InsulKrimp
Type	Spade
UPC	800753095243

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.649/g
Packaging Type	Adhesive Tape on Reel
Stud Size	6 (M3.5)
Wire Insulation Diameter	3.68mm

Wire Size (AWG)	18, 20, 22
Wire Size mm ²	0.25-1.50

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880023</u>
Mini-Mac Pneumatic Applicator for Ring and Spade Terminals, 22-18 AWG	<u>638851300</u>